



Tessera Photometric File Information

When configuring photometric files for Tessera products with multiple LED modules use the instructions below:

For 3203 – Tessera Wall Mount Up/Down Light

Choose files with the appropriate optic and orientation, up file should be stacked above down file with the two files spaced 8.25" apart.

i.e. 3203-12L-40-SP-UP can be combined with 3203-12L-40-WFL-DN to create a single up/down luminaire with a spot optic up and a wide flood optic down, catalog number ordered would be 3203-12L-120-40-SP-WFL-Finish

For 3204 – Tessera Wall Mount Two Module Down Light

Choose files with the appropriate optic, files should be placed side by side spaced 4.125" apart.

i.e. 3204-12L-40-WFL can be combined with 3204-12L-40-WFL to create a double down wall mount luminaire with two wide flood optics, catalog number ordered would be 3204-12L-120-40-WFL-Finish

For 3303 or 3313 – Tessera Wall Mount Up/Down Light

Choose files with the appropriate optic and orientation, up file should be stacked above down file with the two files spaced 12" apart.

i.e. 3303-12L-40-SP-UP can be combined with 3303-12L-40-WFL-DN to create a single up/down luminaire with a spot optic up and a wide flood optic down, catalog number ordered would be 3303-12L-120-40-SP-WFL-Finish

For 3403 or 3413 – Tessera Wall Mount Up/Down Light

Choose files with the appropriate optic and orientation, up file should be stacked above down file with the two files spaced 18" apart.

i.e. 3403-12L-40-SP-UP can be combined with 3403-12L-40-WFL-DN to create a single up/down luminaire with a spot optic up and a wide flood optic down, catalog number ordered would be 3403-12L-120-40-SP-WFL-Finish